


MONET 3.2 SOFTWARE UPGRADE


V. 3.2

Leary's Monet 3.2 software interface is designed to deliver advanced glue application, quality control and data collection in a user-friendly way that automates the manufacturing process and delivers quality product while improving plant efficiencies and throughput.

Monet 3.2 is compatible with the new 55 cm (22 in) SeQure ID widescreen to maximize visual space and improve navigation. This new display offers better touch screen accuracy, improved brightness and contrast and includes a built-in fingerprint reader for securing settings and preventing unauthorised changes. Integrates seamlessly with Leary's vision technologies. See our notable additions to Monet 3.2 below.



Camera Integration



All LearyVIEW camera solutions integrate to Monet 3.2 and offer seamless inspection with on-screen setup and monitoring during production. Monet 3.2 offers remote setup and support from Leary. Camera solutions include options for codes, glue, flaps, skew, print, inserts, Braille and more.

Products Affected

LearyVIEW Camera solutions

View Failed Camera Images




View rejected product inspected by iCode 2D code readers (IC 26, IC 28, IC 36 and IC 37). Rejected products from Leary's full line of camera solutions can now be quickly viewed with a specific reason for the reject. This gives operators immediate real-time visual verification of inspection operation.

Products Affected

iCode

Dual-camera Option




Monet can display (2) LearyVIEW Flex cameras that are used for (1) inspection station. This is most often used with beverage carriers that may require (2) cameras to view all areas of a complex carton.

Products Affected

LearyVIEW Flex

Multi-Touch and Lamp Control




LearyVIEW Flex and Braille has improved viewing with multi-touch pinch zoom. Control the lamp brightness for Flex camera LED in Monet to save with the job setup. Lamp brightness is useful for flaps, folds and skew inspection.

Products Affected

LearyVIEW Flex & Braille

Freeform Gluing




Freeform allows a glue pattern to be placed end-to-end on a glue panel and is ideal for applications with variable product length (such as paper sacks) or to run multiple jobs with differing glue pattern lengths without any setup at changeover.

Products Affected

Array, Sempre-i

Increased Button Security




Button security has expanded to include system settings for LearyVIEW Flex, barcode and Pharmacode solutions. This prohibits operators from accessing and making changes to benchmarked settings without the required approval.

Products Affected

LearyVIEW Flex

Forced Barcode Challenge




Laser 1D and Pharmacode readers can require and force a code challenge at set intervals during production. On-screen notice, buzzer and beacon light is activated until code challenge is performed.

Products Affected

Laser 1D, Pharmacode

Barcode Capabilities




Array controllers are now capable of up to (4) fully featured Laser 1D barcode reader and / or iCode camera stations using the barcode input and (3) additional pattern inputs.

Products Affected

Laser 1D, iCode

Hot Melt Tank Compatible



Monet 3.2 is compatible with the latest series of Robatech hot melt tank which integrates directly to the Monet screen. This allows for simple setup and regulation during operation with one screen.

Products Affected

Robatech hotmelt products

W. H. Leary Co., Inc.
8440 W. 183rd Place, Tinley Park, IL 60487, USA

T: +1(708) 444-4900 E: sales.us@whleary.com